

StirLIN

Up to 3000l/day reliable on site LN₂

Stirling Technology

Since more than sixty years Stirling Cryogenics has designed and manufactured liquid nitrogen production systems, serving customers all over the world under all possible climatic conditions. This experience has culminated in our current range of plants called StirLIN, producing liquid nitrogen in quantities from 60 to more than 3.000 liters per day.

The fully automatic StirLIN allows the user to concentrate on his core activity, eliminating all issues involved with the purchasing and logistics of bulk liquid nitrogen supply.

StirLIN systems

The StirLIN Systems are a popular, plug and produce solution. Taking up little space and ready for work. With the optional chiller no external cooling water supply is needed. Simply connect power and start producing your own liquid nitrogen. The liquid is dispensed through a flexible hose simply by opening a valve. Liquid nitrogen where you need it, when you need it!

Operators only need to replace filters and perform routine checks between maintenance intervals of 6000 operating hours.

Typical StirLIN features

- Easy Installation
- Fully automatic operation by PLC
- Easy liquid nitrogen dispense
- Efficient production
- Low noise level
- Built for stringent climatic conditions
- Connectable to all power supplies
- Worldwide service & maintenance



StirLIN-1
Lite, Economy & Compact



StirLIN-1 Extendible & StirLIN-2



StirLIN-4 (Extendible) & StirLIN-8

Stirling Cryogenics is a registered trade name of DH Industries BV

For more information on the Stirling Cryogenics product range, please contact:
DH Industries BV | Science Park Eindhoven 5003 | 5692 EB Son | The Netherlands
Tel. +31 (040) 2677 300 | Fax +31 (040) 2677 301 | info@dh-industries.com | www.dh-industries.com

StirLIN Options

- Water chiller
- Installation on site
- Consumable parts
- Toolsets
- Maintenance training
- Generator set
- Voltage stabilizer
- Liquid nitrogen handling package
- Remote monitoring
- Automatic transfer system

StirLIN Specifications

	StirLITE	StirLIN-1 Economy	StirLIN-1 Compact	StirLIN-1 Extendible	StirLIN-2	StirLIN-4	StirLIN-4 Extendible	StirLIN-8	
Specifications									
Liquid nitrogen production* at nominal operating conditions [l/h]									
• 1 bar(g) purity 99% nitrogen + inerts	2,9	5,8	11,5	11,5 (99,7%)	23	48	48 (99,7%)	97	
• 3 bar(g) purity 98% nitrogen + inerts	4	7	14	14 (99,5%)	29	64	64 (99,5%)	124	
• 5 bar(g) purity 98% nitrogen + inerts			17	16,5 (99,5%)	33	75	75 (99,5%)	151	
• Other purities					○	○	○	○	
Power consumption** (supplied in 200V-480V, 50Hz-60Hz***) [kW]	8	11	21	27	34	69	77	122	
Water consumption (at 15°C, incl 20% EG) [l/h]	750	750	1.000	1.000	2.000	4.500	4.500	9.000	
Noise [dBA]	72	72	72	72	74	72	72	74	
System size (l x w x h, external chiller not incl.) [m]									
	2,10	2,10	2,10	3,50	3,50	4,90	4,90	4,90	
	2,30	2,30	2,30	3,50	3,50	3,65	4,35	4,35	
	2,15	2,15	2,15	1,80	1,80	2,00	2,00	2,00	
Advised room size (l x w x h, external chiller not incl.) [m]									
	3,75	3,75	3,75	5,00	5,00	6,50	6,50	6,50	
	3,50	3,50	3,50	4,80	4,80	4,80	5,80	5,80	
	3,00	3,00	3,00	3,00	3,00	3,00	3,00	3,00	
Weight [kg]	1.350	1.425	1.500	1.600	2.200	4.000	4.150	5.200	
Liquid nitrogen storage capacity (max pressure 5 barg)****									
• 200 l	●	○							
• 300 l	○	●	○						
• 500 l		○	●						
• 1.000 l				●	●	○	○	○	
• 2.000 l				○	○	●	●	●	

● Standard


○ Option

* Usable liters at atmospheric pressure will be different depending on liquefaction pressure

** Power consumption is excl. Optional chiller

*** Power supply can influence the design and construction

**** Other storage capacities are possible, but not as a standard option



Stirling Cryogenics is a registered trade name of DH Industries BV

For more information on the Stirling Cryogenics product range, please contact:

DH Industries BV | Science Park Eindhoven 5003 | 5692 EB Son | The Netherlands

Tel. +31 (040) 2677 300 | Fax +31 (040) 2677 301 | info@dh-industries.com | www.dh-industries.com